



Actual

**Catalog Number:** ADR99-12D  
**Product ID:** 7TAH006600R0255  
**UPC Number:** 78378661047  
**Status:** Active

Type ADR-ALCUL Single-Conductor, Two-Hole Mount for Conductor Range Max 1000 kcmil, Min 500 kcmil

- Easy Installation - no special tools required.

**North American Specifications (UNSPSC)**

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Dual-Rated Mechanical Connector
Special Features	Easy Installation - no special tools required.
Standard	UL E9809
Number Of Conductors	1
Material	Aluminum
Finish	Tin-Plated
Conductor Range (Main/Primary)	500-1000
Number Of Mounting Holes	2

**Packaging**

Outer Quantity	3
Outer Dimensions (inches)	7.2x5.9x2.2
Weight Uom	69 lbs. per 100

**Documents / Support Tools**

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000390

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com