



TLS 2200®/TLS PC Link™ Labels - # PTL-18-427

MATERIAL: Self-Laminating Vinyl
SIZE: 0.750" W x 1.000" H (19.050 mm W x 25.400 mm H)
QTY/UOM: 250/Roll
CATALOG #: PTL-18-427
PRODUCT #: 18369

\$33.28 MSRP (\$US)

OVERVIEW SPECIFICATIONS

Description for TLS 2200®/TLS PC Link™ Labels

Labels for the TLS 2200® & TLS-PC Link™ Thermal Transfer Portable Printers. Please Note: This material is UL recognized with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

Specification Of TLS 2200®/TLS PC Link™ Labels

Application(s): Panel Identification, Wire & Cable Marking

Agency Approval(s)/Compliance: UL Recognized

Size: 0.750" W x 1.000" H (19.050 mm W x 25.400 mm H)

Printable Area: 0.750" W x 0.375" H (19.050 mm W x 9.530 mm H)

Max Characters Per Line For Font #2: 18

Max Lines of Text For Font #2: 3

Label Type/Style: Self-Laminating Label

Color: White/Translucent

Wire Gauge: 10 to 4

Finish: Matte

Qty Per Row: 1

Material Type: Vinyl

Material Description: Self-Laminating Vinyl

Brady Material #: B-427

Safety Catalog: [pg. 241](#)

General ID Catalog: [pg. 39](#)

Recommended Ribbon Series: R4310

Suggested Ribbon Part#: R4310

Acceptable Ribbon Series: R6210

Printer Compatibility: BMP71, TLS 2200, TLS-PC Link

Special Properties: Excellent abrasion and smudge resistance, Excellent water & oil resistance, Self-Extinguishing, Self-Laminating

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 250/Roll