



Thermal Transfer Printable Labels - # THT-103-423-10

SIZE:	1.000" W x 0.250" H (25.400 mm W x 6.350 mm H)
MATERIAL:	Permanent Polyester
QTY/UOM:	10,000/Roll
CATALOG #:	THT-103-423-10
PRODUCT #:	18658

OVERVIEW

Description for Thermal Transfer Printable Labels

BradyBondz™ polyester labels for thermal transfer printers. Please Note: This material is UL, CSA & AGA approved with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

SPECIFICATIONS

Specification Of Thermal Transfer Printable Labels

Application(s): Circuit Board & Component ID, Through Hole - Top

Agency Approval (s)/Compliance: AGA Approved, CSA Approved, Halogen-Free (DIN VDE 0472/parts 815), UL Recognized

Size: 1.000" W x 0.250" H (25.400 mm W x 6.350 mm H)

Printable Area: 1.000" W x 0.250" H (25.400 mm W x 6.350 mm H)

Web Width: 1.200" (30.48 mm)

Label Type/Style: Label

Vertical Repeat: 0.350" (8.89 mm)

Color: White

Finish: Gloss

Qty Per Row: 1

Material Type: Polyester

Material Description: Permanent Polyester

Brady Material #: B-423

General ID Catalog: pg. 88

Recommended Ribbon Series: 6000

Suggested Ribbon Part#: R6006

Acceptable Ribbon Series: 4900, 6200

Printer Compatibility: BBP81, Brady 1244, Brady 1344, Brady 200MVP Plus, Brady 2461, Brady 300MVP Plus, Brady 300X-Plus II, Brady 3481, Brady 360X-Plus II, Brady 600X-Plus II, Brady 6441, IP300, IP600, Tagus T200, Tagus T300, Thermal Transfer Printers