

BBP®31 and BBP®33 Materials

BradyID.com/bbp31

Indoor/Outdoor Vinyl (B-595)

- For general facility and safety identification: Our best industrial vinyl yet
- Durable, low-shrink vinyl with our most aggressive adhesive
- Conforms to irregular, curved, rough and highly textured surfaces (painted cinder blocks, uneven wood, textured plastics, paper-jacketed pipes, powder-coated surfaces)
- Adheres to “difficult” low-surface energy items (PVC piping, blow-molded equipment cases, ABS plastics, recycled plastics)




Figure 33



Facility and Safety Applications:

- 5S Labels
- Pipe Markers
- Safety & Warning Labels
- Equipment & Panel Labels
- Arc Flash & Chemical Labels
- And More!

Service temp: -40°F to 180°F Application temp: 0°F to 180°F
 Average Outdoor Durability: 8-10 year outdoor vinyl label durability.
 Agency approvals:

Fits Printer Model(s)	Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Roll Length B Feet (m)	Labels Per Roll	Rec. Ribbon
BBP31, BBP33	Fig. 33	B30C-500-595-WT	B-595	White	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-1125-595-WT	B-595	White	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-2250-595-WT	B-595	White	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-3000-595-WT	B-595	White	3.000 (76.2)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-4000-595-WT	B-595	White	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-500-595-YL	B-595	Yellow	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-1125-595-YL	B-595	Yellow	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-2250-595-YL	B-595	Yellow	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-3000-595-YL	B-595	Yellow	3.000 (76.2)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-4000-595-YL	B-595	Yellow	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-500-595-RD	B-595	Red	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-1125-595-RD	B-595	Red	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-2250-595-RD	B-595	Red	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-4000-595-RD	B-595	Red	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-500-595-BL	B-595	Blue	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-1125-595-BL	B-595	Blue	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-2250-595-BL	B-595	Blue	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-4000-595-BL	B-595	Blue	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-500-595-GN	B-595	Green	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-1125-595-GN	B-595	Green	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-2250-595-GN	B-595	Green	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-4000-595-GN	B-595	Green	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-500-595-OR	B-595	Orange	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-1125-595-OR	B-595	Orange	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-2250-595-OR	B-595	Orange	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-4000-595-OR	B-595	Orange	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-500-595-BK	B-595	Black	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-1125-595-BK	B-595	Black	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-2250-595-BK	B-595	Black	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-4000-595-BK	B-595	Black	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-500-595-BR	B-595	Brown	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-1125-595-BR	B-595	Brown	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-2250-595-BR	B-595	Brown	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-4000-595-BR	B-595	Brown	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-500-595-GD	B-595	Gold	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-1125-595-GD	B-595	Gold	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-2250-595-GD	B-595	Gold	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-4000-595-GD	B-595	Gold	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-500-595-GY	B-595	Gray	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-1125-595-GY	B-595	Gray	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-2250-595-GY	B-595	Gray	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-4000-595-GY	B-595	Gray	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-500-595-PL	B-595	Purple	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-1125-595-PL	B-595	Purple	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-2250-595-PL	B-595	Purple	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-4000-595-PL	B-595	Purple	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP31, BBP33	Fig. 33	B30C-500-595-CL	B-595	Clear	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-1125-595-CL	B-595	Clear	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-2250-595-CL	B-595	Clear	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-4000-595-CL	B-595	Clear	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000

U.S. Patent Nos. 5,823,689; 6,570,602. Additional Patents Pending.

View all BBP®33 and BBP®33 Print Ribbon parts on page 379.