

# SPECIFICATIONS

Diameter as Supplied (in/ft/yd)	0.101
Display UoM	Roll of 100 Feet
Maximum Wire Diameter (in/ft/yd)	0.101
Minimum Wire Diameter (in/ft/yd)	0.091
Recovered Diameter (in/ft/yd)	0.091
Roll Length (in/ft/yd)	100
Sleeve Size (in/ft/yd)	0.101 in Dia x 100 ft L
Sleeve Size (mm/cm/m)	2.6 mm Dia x 30.48 m L
Trade Name	BradyMark™
Applications	Cable & Wire Marking
Color	White
For Use with Printer	BRADYMARK™ Hotstamper
Label/Media Format	Roll
Material	Vinyl
Material Properties	Good smear and chemical resistance
Print Technology	Hot Stamping
Resistance Properties	Chemical-Resistant, Smear-Resistant
Suggested Ribbon Series	Hot-Foil