

Rigid and IMC Conduit Fittings

Mighty-Move® Steel Expansion Couplings for Rigid



Assembles like a regular Rigid/IMC set screw coupling. To install, simply slide coupling end stop onto fixed end of conduit and tighten set screw. Place movable conduit end completely into coupling and mark engagement, remove conduit and mark half the distance of engagement, reinstall conduit to half the distance. Bonding jumper purchased separately. US Patent 6,715,803B1.



 File No. E9391

Zinc Plated Steel

Catalog Number	Trade Size	Unit Qty.	Std. Pkg.	Catalog Number	Trade Size	Unit Qty.	Std. Pkg.
EC-075R	3/4"	15	60	EC-250*	2-1/2"	---	1
EC-100R	1"	10	40	EC-300*	3"	---	1
EC-125R	1-1/4"	8	40	EC-350*	3-1/2"	---	1
EC-150R	1-1/2"	6	30	EC-400*	4"	---	1
EC-200R	2"	---	4				

*2 1/2" thru 4" suitable for use with EMT or Rigid/IMC conduit.

Split Rigid Couplings

Split couplings used to join two lengths of threaded rigid and IMC conduit.



 File No. E9391

Zinc Plated Malleable Iron

Catalog Number	Trade Size	Unit Qty.	Std. Pkg.	Catalog Number	Trade Size	Unit Qty.	Std. Pkg.
SRC-050	1/2"	25	100	SRC-250	2 1/2"	---	5
SRC-075	3/4"	10	100	SRC-300	3"	---	5
SRC-100	1"	5	50	SRC-350	3 1/2"	---	4
SRC-125	1 1/4"	---	25	SRC-400	4"	---	5
SRC-150	1 1/2"	---	20	SRC-500	5"	---	2
SRC-200	2"	---	10	SRC-600	6"	---	1