

INDEX BY CATALOG NUMBER

Cat. No.	Page	Cat. No.	Page	Cat. No.	Page
971	222	1072	40	1102-DC	42
972	222	1073	40	1103-DC	42
973	222	1074	40	1104-DC	42
974	222	1075	40	1105-DC	42
975	222	1076	40	1106-DC	42
976	222	1077	40	1107-DC	42
977	222	1078	40	1108-DC	42
978	222	1079	40	1109-DC	42
				1110-DC	42
				1111-DC	42
981	222	1080	40		
982	222	1081	40		
983	222	1082	40	1102-DCI	42
984	222	1083	40	1103-DCI	42
985	222	1084	40	1104-DCI	42
986	222	1085	40	1105-DCI	42
987	222	1086	40	1106-DCI	42
988	222	1087	40	1107-DCI	42
989	222	1088	40	1108-DCI	42
990	222			1109-DCI	42
		1089-1	40	1110-DCI	42
1000	186, 271	1089-2	40	1111-DCI	42
1001	186, 271	1089-3	40		
1002	186, 271	1089-4	40	1121	43
1003	186, 271	1089-5	40	1122	43
1004	186, 271	1089-6	40	1123	43
1005	186, 271	1089-7	40	1124	43
1006	186, 271	1089-8	40	1125	43
1007	186, 271			1126	43
1008	186, 271	1090-1	40	1127	43
		1090-2	40	1128	43
1025	13, 233	1090-3	40	1129	43
1026	13, 233	1090-4	40	1130	43
1027	13, 233	1090-5	40	1131	43
1028	13, 233	1090-6	40	1132	43
1028-XL	13, 233	1090-7	40		
1029	13, 233	1090-8	40	1121-AL	43
1030	13, 233	1090-9	40	1122-AL	43
1030-XL	13, 233			1123-AL	43
		1102	41	1124-AL	43
1061	40	1103	41	1125-AL	43
1062	40	1104	41	1126-AL	43
1063	40	1105	41	1127-AL	43
1064	40	1106	41	1128-AL	43
1065	40	1107	41	1129-AL	43
1066	40	1108	41	1130-AL	43
1067	40	1109	41		
1068	40	1110	41	1121-RT	43
1069	40	1111	41	1122-RT	43
		1112	41	1123-RT	43
1061-RT	41	1113	41	1124-RT	43
1062-RT	41			1125-RT	43
1063-RT	41	1102-I	41	1126-RT	43
1064-RT	41	1103-I	41	1127-RT	43
1065-RT	41	1104-I	41	1128-RT	43
1066-RT	41	1105-I	41	1129-RT	43
1071-RT	41	1106-I	41	1130-RT	43
1072-RT	41	1107-I	41		
1073-RT	41	1108-I	41	1160	44
1074-RT	41	1109-I	41	1161	44
		1110-I	41	1162	44
1070	40	1111-I	41	1163	44
1071	40			1164	44

Rigid and IMC Conduit Fittings

Reducing Washers



To be used in pairs to reduce the size of knockout holes.

UL File No. E11259: 1061 thru 1088

SP File No. LR39354: 1061 thru 1088

Galvanized Steel

Catalog Number	Trade Size	Unit Qty.	Std. Pkg.	Catalog Number	Trade Size	Unit Qty.	Std. Pkg.
1061	3/4" - 1/2"	250	1000	1089-1	3 1/2" - 1/2"	---	10
1062	1" - 1/2"	250	1000	1089-2	3 1/2" - 3/4"	---	10
1063	1" - 3/4"	250	1000	1089-3	3 1/2" - 1"	---	10
1064	1 1/4" - 1/2"	100	500	1089-4	3 1/2" - 1 1/4"	---	10
1065	1 1/4" - 3/4"	100	500	1089-5	3 1/2" - 1 1/2"	---	10
1066	1 1/4" - 1"	100	500	1089-6	3 1/2" - 2"	---	10
1067	1 1/2" - 1/2"	100	200	1089-7	3 1/2" - 2 1/2"	---	10
1068	1 1/2" - 3/4"	100	200	1089-8	3 1/2" - 3"	---	10
1069	1 1/2" - 1"	100	200				
				1090-1	4" - 1/2"	---	10
1070	1 1/2" - 1 1/4"	100	200	1090-2	4" - 3/4"	---	10
1071	2" - 1/2"	50	100	1090-3	4" - 1"	---	10
1072	2" - 3/4"	50	100	1090-4	4" - 1 1/4"	---	10
1073	2" - 1"	50	100	1090-5	4" - 1 1/2"	---	10
1074	2" - 1 1/4"	50	100	1090-6	4" - 2"	---	10
1075	2" - 1 1/2"	50	100	1090-7	4" - 2 1/2"	---	10
1076	2 1/2" - 1/2"	50	100	1090-8	4" - 3"	---	10
1077	2 1/2" - 3/4"	50	100	1090-9	4" - 3 1/2"	---	10
1078	2 1/2" - 1"	50	100				
1079	2 1/2" - 1 1/4"	50	100				
1080	2 1/2" - 1 1/2"	50	100				
1081	2 1/2" - 2"	50	100				
1082	3" - 1/2"	---	25				
1083	3" - 3/4"	---	25				
1084	3" - 1"	---	25				
1085	3" - 1 1/4"	---	25				
1086	3" - 1 1/2"	---	25				
1087	3" - 2"	---	25				
1088	3" - 2 1/2"	---	25				