



# Rigid and IMC Conduit Fittings

## Threaded Hubs



To secure threaded rigid service entrance conduit to box or enclosure. Insulated throat rated 105°C. BUNA-N sealing ring completely encircles knockout to prevent contaminants from entering enclosure. Concrete-tight.

 File No. E9391: Type 4 - Water Tight

 File No. LR39354

Note: UL listing not applicable to 5" & 6" Malleable Iron.

## Zinc Die Cast

Catalog Number	Trade Size	Unit Qty.	Std. Pkg.	Catalog Number	Trade Size	Unit Qty.	Std. Pkg.
151-DC	1/2"	25	100	156-DC	2"	2	20
152-DC	3/4"	25	100	157-DC	2 1/2"	---	10
153-DC	1"	10	50	158-DC	3"	---	5
154-DC	1 1/4"	5	25	159-DC	3 1/2"	1	5
155-DC	1 1/2"	2	20	160-DC	4"	1	5


## Malleable Iron

Catalog Number	Trade Size	Unit Qty.	Std. Pkg.
3161	5"	---	2
3162	6"	---	2

## Lock - A - Liners

Used for converting ordinary bushings and connectors to code approved insulating bushings and connectors without disturbing wiring.



 File No. E11259

## Polypropylene - 105°C

Catalog Number	Trade Size	Unit Qty.	Std. Pkg.	Catalog Number	Trade Size	Unit Qty.	Std. Pkg.
191	1/2"	25	100	194	1 1/4"	10	40
192	3/4"	25	100	195	1 1/2"	10	40
193	1"	25	100	196	2"	10	40