



Rigid and IMC Conduit Fittings

Threaded Hubs



To secure threaded rigid service entrance conduit to box or enclosure. Insulated throat rated 105°C. BUNA-N sealing ring completely encircles knockout to prevent contaminants from entering enclosure. Concrete-tight.

 File No. E9391: Type 4 - Water Tight

 File No. LR39354

Note: UL listing not applicable to 5" & 6" Malleable Iron.

Zinc Die Cast

| Catalog Number | Trade Size | Unit Qty. | Std. Pkg. | Catalog Number | Trade Size | Unit Qty. | Std. Pkg. |
|----------------|------------|-----------|-----------|----------------|------------|-----------|-----------|
| 151-DC | 1/2" | 25 | 100 | 156-DC | 2" | 2 | 20 |
| 152-DC | 3/4" | 25 | 100 | 157-DC | 2 1/2" | --- | 10 |
| 153-DC | 1" | 10 | 50 | 158-DC | 3" | --- | 5 |
| 154-DC | 1 1/4" | 5 | 25 | 159-DC | 3 1/2" | 1 | 5 |
| 155-DC | 1 1/2" | 2 | 20 | 160-DC | 4" | 1 | 5 |


Malleable Iron

| Catalog Number | Trade Size | Unit Qty. | Std. Pkg. |
|----------------|------------|-----------|-----------|
| 3161 | 5" | --- | 2 |
| 3162 | 6" | --- | 2 |

Lock - A - Liners

Used for converting ordinary bushings and connectors to code approved insulating bushings and connectors without disturbing wiring.



 File No. E11259

Polypropylene - 105°C

| Catalog Number | Trade Size | Unit Qty. | Std. Pkg. | Catalog Number | Trade Size | Unit Qty. | Std. Pkg. |
|----------------|------------|-----------|-----------|----------------|------------|-----------|-----------|
| 191 | 1/2" | 25 | 100 | 194 | 1 1/4" | 10 | 40 |
| 192 | 3/4" | 25 | 100 | 195 | 1 1/2" | 10 | 40 |
| 193 | 1" | 25 | 100 | 196 | 2" | 10 | 40 |