

Rigid and IMC Conduit Fittings

Insulated Grounding Bushings



Used with locknut to terminate service conduit to cabinet. Aluminum alloy lug provided for bonding jumper to neutral busbar. Plastic liner prevents damage to wire insulation.

c  us File No. E20412

Malleable Iron / Plastic Metaliner - 150°C

Catalog Number	Grounding Lug Wire Capacity		Trade Size	Unit Qty.	Std. Pkg.
	Min. Solid	Max. Strand			
381	14	to 4	1/2"	50	500
382	14	to 4	3/4"	50	500
383	14	to 4	1"	25	250
384	14	to 1/0	1 1/4"	20	200
384-14	14	to 4	1 1/4"	20	200
385	14	to 1/0	1 1/2"	20	200
385-14	14	to 4	1 1/2"	20	200
386	14	to 1/0	2"	10	100
386-14	14	to 4	2"	10	100
387	14	to 1/0	2 1/2"	---	25
387-40	6	to 250 MCM	2 1/2"	---	25
388	14	to 1/0	3"	---	25
388-40	6	to 250 MCM	3"	---	25
389	14	to 1/0	3 1/2"	---	25
389-40	6	to 250 MCM	3 1/2"	---	25
390	14	to 1/0	4"	---	20
390-40	6	to 250 MCM	4"	---	20
391	6	to 250 MCM	5"	---	5
392	6	to 250 MCM	6"	---	5