

# Rigid and IMC Conduit Fittings

## Insulated Grounding Bushings



Used with locknut to terminate service conduit to cabinet. Aluminum alloy lug provided for bonding jumper to neutral busbar. Plastic liner prevents damage to wire insulation.

c  us File No. E20412

## Malleable Iron / Plastic Metaliner - 150°C

Catalog Number	Grounding Lug Wire Capacity		Trade Size	Unit Qty.	Std. Pkg.
	Min. Solid	Max. Strand			
381	14	to 4	1/2"	50	500
382	14	to 4	3/4"	50	500
383	14	to 4	1"	25	250
384	14	to 1/0	1 1/4"	20	200
384-14	14	to 4	1 1/4"	20	200
385	14	to 1/0	1 1/2"	20	200
385-14	14	to 4	1 1/2"	20	200
386	14	to 1/0	2"	10	100
386-14	14	to 4	2"	10	100
387	14	to 1/0	2 1/2"	---	25
387-40	6	to 250 MCM	2 1/2"	---	25
388	14	to 1/0	3"	---	25
388-40	6	to 250 MCM	3"	---	25
389	14	to 1/0	3 1/2"	---	25
389-40	6	to 250 MCM	3 1/2"	---	25
390	14	to 1/0	4"	---	20
390-40	6	to 250 MCM	4"	---	20
391	6	to 250 MCM	5"	---	5
392	6	to 250 MCM	6"	---	5