



Bridgeport Fittings Inc.
705 Lordship Blvd.
Stratford, CT 06615

Phone: 203-377-5944

Fax: 203-381-3488

Catalog ID:	801-DC2
UPC Number:	78174715801
Description:	Connector, 90 Degrees, Zinc Die Cast, Flex Size 3/8 Inch
Application:	90 Degree fitting with cover recommended cable types used for connecting flexible metal conduit to box or enclosure. 14/4 (.45" 0 min) to 10/4 (.625" 0 max). MC/MCI-A
Trade Size in Inches:	3/8
Knockout Size in Inches:	1/2
Material:	Zinc Die Cast
Finish:	Ball burnished, mirror smooth
Product Note:	HCFMCI-A
Certifications & Codes:	
NEMA Standard:	FB-1
UL Standard:	UL-514B
UL File Number:	E9391
CSA Standard:	LR39354
Federal Standard:	A-A-50552
UNSPSC:	39121419
Country of Manufacture:	USA
Dimensions in Inches:	
Dimension A in Inches:	1-3/8
Dimension B in Inches:	5/8
Dimension C in Inches:	1-1/16
Dimension D in Inches:	1/2
Dimension E in Inches:	.562
Dimension F in Inches:	15/16

