



**Bridgeport Fittings Inc.**  
705 Lordship Blvd.  
Stratford, CT 06615

Phone: 203-377-5944  
Fax: 203-381-3488

<b>Catalog ID:</b>	MCH-075
<b>UPC Number:</b>	78174702345
<b>Description:</b>	Brass Alloy grounding fitting with stainless steel set screws and steel locknut Buna N sealing ring. NPT threads
<b>Application:</b>	The MCH-075 is listed for use in wet & dry locations as a connector for rigid metal conduit or EMT with a Bridgeport Fittings connector. The MCH-075 will provide a wet locations seal when installed with a rated device or enclosure. Rigid Metallic raceways which contain Ground Electrode Conductors (G.E.C.) are required to be bonded at the enclosure and where the conductor exits the raceway for attachment to the ground electrode. The MCH-075 & MCH-100 can be used in both applications: at the enclosure and at the end of the bonding conductor raceway. Not for use in concentric knock-out (K.O.) Patent Pending
<b>EMT Size in Inches:</b>	3/4" with BPT Steel Wet or Dry locations connector
<b>Rigid Size in Inches:</b>	3/4
<b>Knockout Size in Inches:</b>	3/4" NOT for use with Concentric Knock-outs
<b>Cable Size:</b>	Conductor Range: #6 to 4/0 Str. CU
<b>Material:</b>	Brass
<b>Product Note:</b>	Listed for use with Bridgeport Fittings Steel Dry and Wet Location Connectors
<b>Certifications &amp; Codes:</b>	
<b>NEMA Standard:</b>	FB-1
<b>UL Standard:</b>	467
<b>UL File Number:</b>	Listed ETL under Bridgeport Fittings: MCH-075. Conforms to UL 467 and CSA C22.2 No. 18.3

**Federal Standard:** A-A-50553A  
**UNSPSC:** 39121613

Dimensions in Inches:  
**Dimension A in Inches:** 1.68  
**Dimension B in Inches:** 2.06  
**Dimension C in Inches:** .56  
**Dimension D in Inches:** .46

