



SG38ASp

**Bridgeport Fittings Inc.**  
705 Lordship Blvd.  
Stratford, CT 06615

Phone: 203-377-5944  
Fax: 203-381-3488

<b>Catalog ID:</b>	SG38ASP
<b>UPC Number:</b>	78174708570
<b>Description:</b>	Whipper-Snap "U" Shaped Snap-In Connector (Insulated)
<b>Application:</b>	Recommended cable types for connecting 14/4 (.43" 0 min) to 10/3 (.61" 0 max) AC/MC Cable or 3/8" Flexible Metal Conduit to box or enclosure. HCF/HCFMCI-A
<b>Trade Size:</b>	3/8"
<b>Material:</b>	Zinc Die Cast
<b>Product Note:</b>	CSA listed for use with 14/2 to 10/3 ACG90
Certifications & Codes:	
<b>NEMA Standard:</b>	FB1
<b>UL Standard:</b>	UL514B
<b>UL File Number:</b>	E20534
<b>Federal Standard:</b>	A-A-50552
<b>UNSPSC:</b>	39121438
<b>Patent Number:</b>	7,064,272
<b>Country of Manufacture:</b>	USA
Dimensions in Inches:	
<b>Dimension A in Inches:</b>	13/32
<b>Dimension B in Inches:</b>	5/8
<b>Dimension C in Inches:</b>	1-1/16

