

[BATH/VENTILATION FANS](#)
[RANGE HOODS](#)
[CEILING FANS](#)
[CENTRAL VACUUM SYSTEMS](#)
[DOOR CHIMES](#)
[INTERCOM SYSTEMS](#)
[IRONING CENTERS](#)
[MEDICINE CABINETS](#)
[HOME THEATER/AUDIO](#)
[CUSTOMER RESOURCES](#)
[CodeKey™ - Whole House Mechanical Ventilation Specifier Tool](#)
[DOWNLOAD NUTONE CATALOGS](#)
[ORDER REPLACEMENT PARTS](#)

[NuTone NEWS](#)

NuTone Fans Set New Revolutionary Standard for Fast Installation, Quiet Ventilation
[Find out More](#)

NuTone LunAura Collection Offers First Ambient LED Soft-Glo Ventilation Fans
[Find out More](#)

NuTone Ceiling Fans – Create a Cool, Soothing Breeze Both Indoors and Out
[Find out More](#)

NuTone® Storage Solutions Safeguard the Home and Family.
[Find out More](#)

Make a Stunning First Impression with New Decorative Chime Pushbuttons from NuTone®.
[Find out More](#)

Humidity Sensing Recessed Fan/Light from NuTone® awarded a Most Valuable Product Award.
[Find out More!](#)

Ultra Silent™ Ventilation Fans Provide More Light Using Less Energy
[Find out More!](#)

NuTone® Offers American Made ENERGY STAR® Fan Line-Up
[Find out More!](#)

[More News Releases](#)

In U.S.A. Call: 888-336-3948
 Technical Support: 888-336-6151
 In Canada Call: 888-882-7626
 For Canadian products please visit nutone.ca

Discontinued Products Discontinued Products - Audio



This model is no longer for sale

Two-Way, Indoor/Outdoor (Weather Resistant) Surface Mount Speakers

Model SS523WH

- Frequency response: 100 - 20,000Hz ±3dB
- Power handling capacity: 50 Watts RMS
- 3-1/4" Mica impregnated cone woofer, 1" Polycarbonate dome tweeter
- Sensitivity: @ 1 meter with 1 Watt input: 85dB
- Overall dimensions: 4-1/2" H x 7" W X 4-1/4" D
- Color: White

Contact your [local dealer](#) for pricing information on all NuTone products except range hoods.

Additional Models Available:

IS9523BL	Outdoor, Weather-Resistant, Surface-Mounted, Black, Two-Way Speaker
IS9523WH	Outdoor, Weather-Resistant, Surface-Mounted, White, Two-Way Speaker
IS9625WH	Indoor Two-Way Built-In Speaker
IS9626WH	Indoor Two-Way Built-In Speaker
IS9825WH	Indoor Two-Way In-Wall Speaker
NS382CWH	Indoor 8" 2-Way In-Ceiling Intercom Speaker
SS4108P	8" Powered Subwoofer
ES4110PB	Powered Subwoofer
ES628DS	Two-Way, In-Ceiling, Weather Resistant, Indoor/Outdoor
ES828	Two-Way, In-Wall Speaker
ES838	Three-Way, In-Wall Speaker, Indoor
GS625	Two-Way in Ceiling, Indoor Speaker
GS626DS	Two-Way, In-Ceiling, Weather Resistant Speaker, Indoor/Outdoor
HO33090	Top Lights for Surface Mount Cabinets
HTIB600WBL	600 Watt Home Theater in a Box
IR668	Rough-In
IR884	Rough-In
IR885	Rough-In
IR886	Rough-In
IS82	5" Indoor Speaker - Bright White
IS920WH	5" Two-Way Round Indoor Speaker - White
ISA335BL	5" Indoor Speaker w/Controls - Black
ISA338D	8" Indoor Speaker w/Controls - Sable Brown
MS8W4	4" Micro Speaker (sold in pairs)
SS326C	6-1/2" Two-Way, Weather Resistant, Indoor/Outdoor Rock Speakers
SS326G	6-1/2" Two-Way, Weather Resistant, Indoor/Outdoor Rock Speakers
SS326R	6-1/2" Two-Way, Weather Resistant, Indoor/Outdoor Rock Speakers
SS4110PB	In Wall Power Subwoofer
SS523BL	Two-Way, Indoor/Outdoor (Weather Resistant) Surface Mount Speakers
SS523WH	Two-Way, Indoor/Outdoor (Weather Resistant) Surface Mount Speakers
SS725	Two-Way Center Channel Speaker

