

JC Bi-Pin - 120V (GY6.35)

Products > HALOGEN > Line Voltage Bi-Pins > JC Bi-Pin - 120V (GY6.35)

- Provides UV protection
- Filament types include C-2, CC-8
- Ideal for residential and commercial applications, for both indoor and outdoor use



Chandelier Landscape Track

Technical Specifications

Watts	Bulb Type	Base	Item #	Ordering Code	Volts	Inner Pk. / Master Ctn.	Description	Lumens	Average Hours	MOL	Beam	Color Temperature	Color Description	CRI	M.O.D.
20	T4	G6.35	652020	Q20GY6/120	120	10 / 50	Clear	330	2000	1.6"	-	2900K	Soft White	100	0.5"
35	T4	G6.35	652035	Q35GY6/120	120	10 / 50	Clear	650	2000	1.75"	-	2900K	Soft White	100	0.5"
50	T4	G6.35	652050	Q50GY6/120	120	10 / 50	Clear	950	2000	1.75"	-	2900K	Soft White	100	0.5"
75	T4	G6.35	652075	Q75GY6/120	120	10 / 50	Clear	1300	2000	1.75"	-	2900K	Soft White	100	0.5"
100	T4	G6.35	652100	Q100GY6/120	120	10 / 50	Clear	1900	2000	1.75"	-	2900K	Soft White	100	0.5"
150	T4	G6.35	652150	Q150GY6/120	120	10 / 50	Clear	2300	2000	2"	-	2900K	Soft White	100	0.5"