

**MY28, MY29 Series**

**DIELESS HYTOOL™**

#8 Str. through 250 kcmil Copper,  
#8 Str. through 4/0 str. Aluminum  
Conductors

**Features and Benefits**

- Save on capital investment with the type MY HYTOOL™ that accommodates a wide range of connector/conductor combinations from #8 str.-250 kcmil
- Save time, money, and lower installed cost with the original dieless MY tool design. No separate dies required to purchase or to lose
- Fast and easy tool setting for the connector/conductor combination simply by aligning the white scribe on the nest die with the wire size on the gauge for proper crimping results
- Easy to adjust nest die with knurled steel knob and machine threads
- Quality tool with precision machines indenter, component parts and tool body
- Fast, medium and high volume crimping is easily accomplished by bench mounting the type MY tool in the BMY-BCH-MT bench mount adapter. A single bolt holds the MY HYTOOL™ securely using the 0.31 dia. mounting hole in the bench mount adapter



- High quality rugged tool design manufactured from heavy duty forged steel with strong reinforced back and handles
- Covered handles available on the MY29-3C, MY29-11C and MY29-3CF HYTOOL™
- Comfort grip handles for long periods of usage
- Compression terminals and splices are UL Listed and CSA Certified when installed with type MY HYTOOL™
- 5-year limited warranty

**SPECIFICATIONS**

**Length:** 22.65"  
**Weight:** 8 lbs approx.  
**Depth:** 4.86"  
**Width:** 1.12"

**FOR USE ON**

TOOL	CONNECTORS
<b>MY29-3</b> <b>MY29-3C</b> <b>MY29-3CF</b>	Copper-YA, YA-L, YS-L Aluminum-YA-A, YS-A
<b>MY29-11</b> <b>MY29-11C</b>	Copper-YA, YA-L, YS YAV-FX YS-L, YAV-L, YSV-L
<b>MY28</b>	YAV-L, YSV-L
<b>MY28-4</b>	YAV-A-L, YSV-A-L, YAV-A-R
<b>MY28-6</b>	YAE-L, YAEV-RS, YAEV-H, YAEV-RH

**ACCESSORIES**

**BMY-BCH-MT** Bench Mount Adapter

**MY29 UNIVERSAL KIT** Contents:

MY29-11	1 EA
YA8CLBOX	50 EA
YAV6CLTC14FX	50 EA
YAV4CLTC516FX	50 EA
YAV2CLTC516FX	50 EA
YAV1CLTC38FX	50 EA
YAV25LTC38FX	10 EA
YAV26LTC516FX	10 EA
YAV27LTC12FX	10 EA
YAV28LTC12FX	10 EA
YA29LBOX	10 EA
CASE	1 EA

<b>MY29-3</b>	#8 str.-250 kcmil Copper commercial (code) cable
<b>MY29-3C</b> (covered handles)	30 Navy-250 Navy Copper Navy Cable
<b>MY29-3CF</b> (fully covered)	#8 str.-4/0 str. Aluminum commercial (code) cable
<b>MY29 UNIVERSAL KIT</b>	#8 str.-250 kcmil Copper commercial (code) cable
<b>MY29-11</b>	30 Navy-250 Navy Copper Navy cable
<b>MY29-11C</b> (covered handles)	#8 str.-4/0 str. Flexible copper mine machine cable
<b>MY28</b>	#8 str.-4/0 str. Copper aircraft cable
<b>MY28-4</b>	#8 str.-4/0 str. Aluminum aircraft cable
<b>MY28-6</b> (nylon covered connector)	#8 str.-2/0 str. Copper aircraft cable (flexible)

