

AYP750 : 700/750
AL HYPLUG

ACTIVE



Experience. Technology. Answers.™

www.burndy.com

BURNDY® PRODUCTS

Specifications

Dimensional

B Length (Fraction)	1-5/8
B Length (in)	1.59
Strip Length	1-3/4
Pin Length (in)	1.76

General

Product Description	Aluminum Compression Pin Adapter, 700/750 kcmil, 0.81" Plug Dia, 1.76" Plug Length, Al/Cu Rated, Tin Plated
----------------------------	---

Conductor(s)

Aluminum Size (Range)	700 kcmil-750 kcmil
Copper Stranded (Range)	700 kcmil-750 kcmil

Physical

Type of Plating	Tin - Electro Plated
Insulation Type	Rubber
Pin Type	Straight
Plated (Yes or No)	Y
Index Number	936
Product Material	Aluminum
Insulated (Yes or No)	Y

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Other Features

UPC	78181073778
------------	-------------