



BURNDY Catalog Number	GAR8629
UPC Number	781810030929
Description	2/0-250CU 6IPS
Status	Active

Web Use
BURNDY Product Line

Dimensional

Width (in)	8.38
Length (in)	1.81
Height (in)	8.81
Size (Hex) or Size (Bolt)	1/2
Size (Hex) or Size (Bolt) - in	0.5
B Length (in)	1.25
Width (Fraction)	8-3/8
Height (Fraction) (in)	8-13/16

General

Product Description	Fence Post Grounding Connector, 2/0 Sol. - 250 kcmil, Bright Dipped
---------------------	--

Conductor(s)

Copper Tube Size (SCH40) - Range	6 IPS IPS
Rod Size (Range)	N/A
Copper Solid Size (Range)	2/0 AWG-4/0 AWG
Copper Stranded (Range)	1/0 -250 kcmil
Rebar Size (Range)	N/A

Physical

Type of Hardware	DURIUM® Silicon Bronze
Installation Torque	480
Type of Plating	Unplated
Plated (Yes or No)	N
Product Material	Copper Alloy

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N
Industry Standards	UL467
Rated for Direct Burial Documentation	Y

For further technical assistance, please contact us

47, industrial Park Drive
Manchester NH03109

47, industrial Park Drive
Manchester NH03109

Monday - Friday
Phone: 000-346-4175