



Type KC22B2

1/2-13
stud size

BURNDY Catalog Number KC22J12T13
 UPC Number 781810127872
 Description SERVIT POST MALE
 Status Active

Web Use
 BURNDY Product Line

	Dimensional
Thread Size	1/2-13
Length (in)	1.5
Height (in)	1
Size (Hex) or Size (Bolt)	1/2
B Length (in)	0.41
	General
Product Description	Leaded Commercial Transformer Ground Connector, 8 Sol.-2 Sol. AWG, 1.50 in L, .88 in W
	Conductor(s)
Copper Solid Size (Range)	8 AWG-2 AWG
Copper Stranded (Range)	N/A
	Physical
Installation Torque	80
Type of Plating	Unplated
Plated (Yes or No)	N
Product Material	Leaded Bronze Alloy
	Approvals / Certifications
Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

BURNDY Technical Servcies

Hours: 8.00 AM - 5.00 PM

Monday - Friday

Phone: 000-346-4175

47, industrial Park Drive
 Manchester NH03109

47, industrial Park Drive
 Manchester NH03109