

**FASTAP™ with
Lineman Assist™**

ACCOMMODATES: AAC, AAAC, ACSR, ACAR, Messenger Guy and Copper Conductors

MATERIAL: Aluminum
Galvanized steel hardware

The BURNDY FASTAP™ with Lineman Assist™ utilizes a spring system that acts as a third hand to assist in installation. This system helps secure the tap conductor while installing on Primary, Secondary, and service applications. Duck bill handle simplifies installation by providing a handle to easily hold the connector while wearing dielectric gloves. Conductor side entry facilitates installation and helps keep inhibitor in the connector. Strip sealed and prefilled with PENETROX™ joint compound to limit oxide growth and increase the life of the connection.

Available Options:

- Remove "S" for no PENETROX™
- Add "SS" for stainless steel hardware
- Add "C" to include a cover
- Add "HN" for shear nut
- Cover may be ordered separately (UCTCOVER)



Not recommended for Copper to Copper applications; use copper connector.

To ensure proper tightening torque, use BURNDY® BTW Torque Wrenches.

Meets ANSI C119.4 Class A Heat Cycle & Class 3 Tension.

Catalog Number	Conductor Range				Conductor Diameter				Torque (in-lb)	Wrench Size	Dimensions		
	Groove A (Run)		Groove B (Tap)		Groove A (Run)		Groove B (Tap)				L	H	W
	Copper & Aluminum	ACSR, 6201 & 5005	Copper & Aluminum	ACSR, 6201 & 5005	Min	Max	Min	Max					
UCT26RS	8 Sol - 2/0 Str	6 Str - 2/0 Str	8 Sol - 2/0 Str	6 Str - 2/0 Str	.13	.45	.13	.45	250	9/16	1.62	2.62	2.50
UCT32RS	1 Sol - 400 kcmil	2 Str - 336.4 kcmil	8 Sol - 4/0 Str	6 Str - 4/0 Str	.29	.73	.13	.56	250	9/16	1.62	2.62	2.82

UCTCOVER

FASTAP™ COVER

For Selected UCT and UCG Tap Connectors

High density Polyethylene cover accommodates all FASTAP™ connectors and select UCG connectors. One piece design. Simply slip over the connection and snap shut. Supplied in black.

- UCTCOVER** for use with:
- UCT26RS**
 - UCT32RS**
 - UCG32RS**
 - UCG25RS**



Blue highlighted items are industry standard and most frequently ordered.