

**YA39A5 : 750 AL 2-  
HOLE 1/2**



ACTIVE



*Experience. Technology. Answers.™*

[www.burndy.com](http://www.burndy.com)

**BURNNDY® PRODUCTS**

**Specifications**

<b>Dimensional</b>	
Tongue Angle	Straight
Strip Length	2 7/8
Length (in)	7.07
Tongue Type	Standard
Bolt Hole Size (in)	0.52
Thickness	0.43
B Length (in)	2.46
Pad Width (in)	1.62
E - in	1.75
<b>General</b>	
Number of Holes	2
Product Description	Aluminum Compression Lug, 2 Hole w/o Inspection Window , 750 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Al/Cu Rated, Tin Plated
<b>Conductor(s)</b>	
Aluminum Size (Range)	700 kcmil-750 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	700 kcmil-750 kcmil
<b>Physical</b>	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/2
Color Code	Yellow
Plated (Yes or No)	Y
Index Number	936
Product Material	Aluminum
<b>Approvals / Certifications</b>	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
Industry Standards	UL468A-468B