






No.	REVISED	DRAWN	DATE
1			
2			



L
1 - 3 ft +2/-0 cm
4 - 10 ft +2/-1 cm
11 - 20 ft +3/-1 cm




- 1. ORANGE
- 2. WHITE/ORANGE
- 3. LIGHT BLUE
- 4. WHITE/LIGHT BLUE
- 5. BROWN
- 6. WHITE/BROWN
- 7. LIGHT GREEN
- 8. WHITE/LIGHT GREEN

CONNECTIONS

P1	COLOR	P2
1	OR/WH	1
2	OR	2
3	GN/WH	3
4	BL	4
5	BL/WH	5
6	GN	6
7	BR/WH	7
8	BR	8

Name & Description

No.:	Name & Description	Q'ty
1	CAT.5E UTP 24AWG(0.195x7) x 4P , OD:5.4±0.15mm	1 pcs
2	CP/8x8 PLUG (#P8-006 ), PLATED GOLD 50u"	2 pcs
3	LABLE	2 pcs
4	1PC/CP C5E BAG,10PCS/CASE BAG ,BROWN BOX.	
CABLE MARKING:		
350MHZ ETL VERIFIED ANSI/TIA 568B.2 CATEGORY 5E CM 75°C UTP PATCH		
CORD 4PAIR 24AWG E197532 xxxxxxM		



SCALE 1:1

ITEM N.O.:C5E-O PATCH  
 DRW DATE: 2011-7-15  
 CHANGING DATE:

DRAWN BY: Pingdeng .D  
 CHECKED BY: *Jane Shaw*  
 APPROVED BY:

CUSTOMER BY:  
 APPROVED BY:  
 3 R D

