


L	
1 - 3 ft	+2/-0 cm
4 - 10 ft	+2/-1 cm
11 - 20 ft	+3/-1 cm




- |                     |                      |
|---------------------|----------------------|
| 1. ORANGE           | 5. BROWN             |
| 2. WHITE/ORANGE     | 6. WHITE/BROWN       |
| 3. LIGHT BLUE       | 7. LIGHT GREEN       |
| 4. WHITE/LIGHT BLUE | 8. WHITE/LIGHT GREEN |

CONNECTIONS

P1	COLOR	P2
1	ORWH	1
2	OR	2
3	GNWH	3
4	BL	4
5	BLWH	5
6	GN	6
7	BRWH	7
8	BR	8

No.:	Name & Description	Q'ty
1	CAT.6 UTP 24AWG(0.195x7) x 4P , OD:5.4±0.15mm	1 pcs
2	P8-S59 8P8C 2L PLUG , PLATED GOLD 50u"	2 pcs
3.	MOLDING SR	2 pcs
4	LABLE	2 pcs
5	1PC/CL C6 BAG, 10PCS/CASE BAG, CLEARLINKS WHITE BOX	
CABLE MARKING:		
550MHZ ETL VERIFIED ANS/ITIA 568C.2 CATEGORY 6 CM (UL) 75°C UTP PATCH		
CORD 4PAIR 24AWG E197532 xxxxxxft		



SCALE 1:1

ITEM N.O.:CP-C6-M PATCH  
 DRW DATE: 2012-8-8  
 CHANGING DATE:

DRAWN BY: Pingdeng .D  
 CHECKED BY: *Jane Zhou*  
 APPROVED BY:

CUSTOMER BY:  
 APPROVED BY:  
 3 RD