



Representative

Catalog Number: 273PSA-21
Product ID: 7TAA124710R0006
UPC Number: 78378663714
Status: Active

Shielded Surge Arrester, PSA Parking Stand Arrester, 25kV, MCOV KV RMS is 17.00

North American Specifications (UNSPSC)

UNSPSC	39121634 Surge arrester
IGCC	4988 Surge arrester
Brand Name	Elastimold
Type	Parking Stand Surge Arrester
Special Features	EPDM Rubber Construction - Fully Shielded and Fully Submersible for a Variety of Applications. IEEE 386 Interfaces Provide Convenient Energized Connection with other 200 Amp Loadbreak or Deadbreak Components. Compact Size Enables Installation in your Existing Cabinetry, Saving you Money. Number 4 AWG Ground Lead Tethered to the Jacket Withstands 10,000 Amps for 10 Cycles without Fusing. Ground Lead Also Controls ENd Plug when Ejected, Preventing Uncontrolled Trajectory and Maintains the Housing Shield Ground Connection After Failure.
Application	Provide High Voltage Lightning and Switching Surge Protection of Tranformers, Cable, Equipment and other Components typically Located on Underground Power Distribution Systems.
Voltage Rating	25kV
Amperage Rating	200 Amp
Insulation	Yes
Material	EPDM Molded Rubber

Packaging

Outer Quantity	1
Outer Dimensions (inches)	15.5x10.5x3.5
Weight Uom	6.85 lbs. Each

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com