



Actual

Catalog Number: IPC4141
Product ID: 7TAH006420R0033
UPC Number: 78378633112
EAN Number: 05415022245127
Status: Active

Type IPC - Talon Insulation Piercing Connector for Conductor Range Main: 4/0-1/0 AWG, 95-50 MM sq., Tap: 4/0-1/0 AWG, 95-50 MM sq.

- For copper-to-copper, copper-to-aluminum and aluminum-to-aluminum applications (insulated conductor only). Performs as splice or tab for non-tension applications up to 600 volts, depending on size of connector.
- Self-insulated for hot line applications. Six sizes cover range from #10 to 500 kcmil.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Insulated Conductor Connectors
Special Features	For copper-to-copper, copper-to-aluminum and aluminum-to-aluminum applications (insulated conductor only). Performs as splice or tab for non-tension applications up to 600 volts, depending on size of connector.
Standard	UL E9809
Temperature Rating	90 Degrees C Max
Conductor Range (Main/Primary)	4/0-1/0 AWG, 95-50 MM sq.
Conductor Range (Tap/Secondary)	4/0-1/0 AWG, 95-50 MM sq.
Number Of Mounting Holes	2

Packaging

Inner Quantity	30
Outer Quantity	120
Outer Dimensions (inches)	17.2x14.1x8.3
Weight Uom	53.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com