

# Calbrite™

## Stainless Steel Conduit Systems

### Stainless Steel FDC Single Gang Device Boxes

#### Features:

- Manufactured in type 316 stainless steel for increased corrosion resistance
- Polished with standard "brite" finish to increase corrosion resistance and aesthetic appearance
- Machined standard NPT threads
- Internal grounding screw included
- Manufactured with mounting feet
- No package qty. required
- Ports located on the top & bottom



#### Certifications and Compliances:

UL514A approved – file # E307133

Material: Body - CF8M (316)

Grounding Screws: 316SS

Standards: ASTM A351

#### Applications:

Used for wiring devices, such as switches and receptacles

#### Industries Commonly Served:

- Food & Beverage Production & Distribution
- Chemical Plants
- Water & Wastewater Treatment
- Pharmaceuticals & Cosmetics
- Refining & Extraction Sites
- Petrochemical Operations
- Marine & Coastal Facilities
- Pulp and Paper Mills
- Along with other corrosive environments



Size	Part Numbers	Overall Length	Overall Width	Depth	Cubic In.	Center Hole to Center Hole	Mounting Feet Hole Dia.	Weight (ea) per lb.
¾"	S60700FDCS	5.950"	2.830"	2.500"	25"	3.300"	5/16"	2.40
1"	S61000FDCS	6.300"	2.830"	2.500"	25"	3.300"	5/16"	3.10

*All dimensions are for informational purposes only \* Tolerances +/- 5%*