

Calbrite™

Stainless Steel Conduit Systems

Stainless Steel TB Condulet

Features:

- Manufactured in type 316 stainless steel to meet any stringent sanitary condition
- Polished with standard "brite" finish to increase corrosion resistance and aesthetic appearance
- Designed for use with stainless threaded conduit
- Solid stainless construction permits easy installation using ordinary hand tools
- The flat back design allows extra wiring capacity
- No package qty. required
- Cover & Gasket included
- Form 8 Style



Certifications and Compliances:

UL514A approved
UL File Number – E307133

Material:


Material: Body CF8M- 316SS
Gasket - Neoprene
Cover & Screws: 316SS

Applications:

To connect and change direction of conduit runs
Can be used as pulling fittings
Accessible wiring chamber provides a spacious location to make splices

Industries Commonly Served:

- Food & Beverage Production & Distribution
- Chemical Plants
- Water & Wastewater Treatment
- Pharmaceuticals & Cosmetics
- Refining & Extraction Sites
- Petrochemical Operations
- Marine & Coastal Facilities
- Pulp and Paper Mills
- Along with other corrosive environments



Size	Part Number	A	B	C	a	Cubic Inches	Weight (ea) per lb.
1/2"	S60500TB00	5.690"	1.350"	2.500"	4.320"	5"	1.08
3/4"	S60700TB00	6.270"	1.600"	2.720"	4.940"	9"	1.50
1"	S61000TB00	7.320"	1.770"	3.100"	5.650"	13"	2.28
1-1/2"	S61500TB00	10.40"	2.560"	4.290"	7.810"	35"	4.90
2"	S62000TB00	12.30"	3.500"	4.640"	10.00"	77"	9.32

*All dimensions are for informational purposes only *Tolerances +/- 5%*