

## Specification Sheet

# BR38 Incandescent Reflector Lamp (Indoor/Outdoor Use)

Item Number **04414**

### Specifications

Energy Used (Watts).....	100
Domestic Code.....	100BR38/B/FL
Volts.....	120
Beam Type.....	Flood
Filament Type.....	C9
Light Center Length (LCL).....	3 5/8"
Average Rated Hours.....	2000
Life (in years)*.....	1.8
Estimated Yearly Energy Cost**.....	\$12.05
Country of Origin.....	China



### Physical Characteristics

Finish.....	Blue
Base.....	E26 (Medium)
MOL.....	5 3/4"

\* Based on 3 hrs./day

\*\* Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com)

Westinghouse Lighting Corporation, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting Corporation, a Westinghouse Electric Corporation licensee  
 © "Westinghouse" and "You can be sure...if it's Westinghouse" are all registered trademarks of Westinghouse Electric Corporation

