




Part #	15T6-145V				
Description	T6 145V 15W E12 BASE				
Bulb Shape	T-6	Filament	C-7A	Base Style	Candelabra Screw (E12)
Glass Diameter (in)	0.75	MOL[†] (in)	3.06	LCL^{††} (in)	0.00
Glass Diameter (mm)	19	MOL (mm)	77.80	LCL (mm)	0.00
Volts	145	MSCP[‡]	6	Avg Life Hrs	2000
Watts	15	Amps	0.10	RoHS Compliant	
E-Marked	No	Drawing	 15T-6 145V.pdf	New Announcement	