



Watts	Bulb	Base	Description	Volts	Pkg. Qty.	Rated Avg. Life (Hrs)	Filament	MOL (in.)	Apprx. Lumen	
20	T6 1/2	Int	20T61/2/IF/INT	Exit Sign	130	25	5000	C-8	5 1/2	90
			20T61/2/CL/INT	Exit Sign	130	25	5000	C-8	5 1/2	90
		DC	20T61/2/IF/DC	Exit Sign	130	25	5000	C-8	5 1/2	90
			20T61/2/CL/DC	Exit Sign	130	25	5000	C-8	5 1/2	90