



GE
Lighting

47724 - GE Heat Lamp Saf-T-Gard® R40 - Shatter-Resistant; Heat Lamp

250R40/1/STG PQ6

- ☞ GE's specialty bulbs offer innovative solutions for a variety of lighting needs.
- ☞ Shatter Resistant Bulb - Protective coating helps contain glass fragments if broken.

Product Photo



CAUTIONS & WARNINGS

Warning

Risk of Burn

Do not touch operating lamp.

Risk of Fire

Keep combustible materials away from lamp.

Use in fixture rated for this product.

Lamp emits IR radiation which may cause eye injury

Do not use on infant

disabled

sleeping

or unconscious person or any person/animal unable to avoid potential injury.

Use in fixture approved for this product.

GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Filament	C-9
Rated Life Hours-nominal	5000 h
Primary Application	Shatter-Resistant Heat Lamp
Product Technology	Incandescent
Base	E26
Bulb Shape	R40

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	9
Initial Lumens-nominal	2150 lm

PRODUCT INFORMATION

Product Code	47724
Description	250R40/1/STG PQ6
Alternative Unit Of Measure	CASE

DIMENSIONS

Diameter	2.62 in
----------	---------

ELECTRICAL CHARACTERISTICS

Wattage	250 W
Input Voltage [nom]	120 V