

DC Bayonet Base													
Watts [W]	Volts [V]	Product Code	Product Description	Product Comparison	Case Qty	Initial Lumens [lm]	Average Life Hours	Color Temp. (K)	Filament	M.O.L.		L.C.L.	
										(in.)	(mm)		(in.)
50	120	81805	50Q/CL/DC	50Q/CL/DC	50	725	1500	2850	CC-8	2.48	63	1.30	33
	120	82001	50Q/DC	50Q/F/DC	50	690	1500	2850	CC-8	2.48	63	-	-
	130	81854	50Q/CL/DC	50Q/CL/DC/130V	50	725	1500	2850	CC-8	2.48	63	1.30	33
	130	82013	50Q/DC	50Q/F/DC/130V	50	1150	1500	2850	CC-8	2.48	63	-	-
75	28	82148	75Q/CL/DC/28V	75Q/CL/DC/28V	50	1350	2000	2950	CC-8	2.36	60	1.46	37
	120	82099	75Q/CL/DC	75Q/CL/DC	50	1050	1500	2850	CC-8	2.48	63	1.30	33
	120	82246	75Q/DC	75Q/F/DC	50	1150	1500	2850	CC-8	2.48	63	-	-
	130	82081	75Q/CL/DC	75Q/CL/DC/130V	50	1050	1500	2850	CC-8	2.48	63	1.30	33
100	130	82253	75Q/DC	75Q/F/DC/130V	50	1150	1500	2850	CC-8	2.48	63	-	-
	120	80188	100Q/CL/DC	100Q/CL/DC/ESN	50	1600	1500	2850	CC-8	2.48	63	1.30	33
	120	80343	100Q/DC	100Q/F/DC	50	1520	2000	2850	CC-8	2.48	63	-	-
	130	80237	100Q/CL/DC	100Q/CL/DC/130V	50	1600	2000	2850	CC-8	2.48	63	1.30	33
150	130	80384	100Q/CD	100Q/F/DC/130V	50	1520	2000	2850	CC-8	2.48	63	-	-
	120	80482	150Q/CL/DC	150Q/CL/DC/ETC	50	2800	2000	2850	CC-8	2.48	63	1.30	33
	120	80678	150Q/DC	150Q/F/DC/ETF	50	2660	2000	2850	CC-8	2.48	63	-	-
	130	80531	150Q/CL/DC	150Q/CL/DC/130V	50	2800	2000	2850	CC-8	2.48	63	1.30	33
250	130	80727	150Q/DC	150Q/F/DC/130V	50	2660	2000	2850	CC-8	2.48	63	-	-
	120	80874	250Q/CL/DC	250Q/CL/DC/ESS	50	5000	2000	2900	CC-8	2.96	75	1.65	42
	120	81070	250Q/DC	250Q/F/DC/ETB	50	4750	2000	2900	CC-8	2.96	75	-	-
	130	80923	250Q/CL/DC	250Q/CL/130V	50	5000	2000	2900	CC-8	2.96	75	1.65	42
400	130	81119	250Q/DC	250Q/F/DC/130V	50	4750	2000	2900	CC-8	2.96	75	-	-
	120	81266	400Q/CL/DC	400Q/CL/DC	50	8250	2000	2900	CC-8	3.54	90	1.89	48
	120	81364	400Q/DC	400Q/F/DC	50	7840	2000	2900	CC-8	3.54	90	-	-
	130	81275	400Q/CL/DC	400Q/CL/DC/130V	50	8250	2000	2900	CC-8	3.54	90	1.89	48
500	130	81370	400Q/DC	400Q/F/DC/130V	50	7840	2000	2900	CC-8	3.54	90	-	-
	120	81438	500Q/CL/DC	500Q/CL/DC	50	10450	2000	2950	CC-8	3.54	90	1.89	48
	120	81609	500Q/DC	500Q/F/DC	50	9930	2000	2950	CC-8	3.54	90	-	-
	130	81462	500Q/CL/DC	500Q/CL/DC/130V	50	10450	2000	2950	CC-8	3.54	90	1.89	48
	130	81658	500Q/DC	500Q/F/DC/130V	50	9930	2000	2950	CC-8	3.54	90	-	-