

You are here

## 60-Watt Rough Service Incandescent A19 MED Frost



Litetronics.com



### *Rough Service™*

**Markets**

- Restaurants
- Hospitality
- Casino
- Cinema
- Agriculture

**Applications**

- General Lighting
- Table and Floor Lamps

**Product Description**

Rough Service incandescent light bulbs have an unprecedented 20,000-hour rated life – that's up to 28 times longer than the life of a standard incandescent light bulb! Rough Service light bulbs boast a durable seven-support filament mounting, triple alloy tungsten filament, brass base to prevent corrosion, and three separate getters.

This 60-watt A19 Rough Service incandescent light bulb has a frost finish and provides 560 lumens. It is ideal for outdoor signs and hard-to-reach places, where its super long life will drastically reduce maintenance and replacement costs.

**Literature**

- [Material Safety Data Sheet](#)
- [Rough Service Enlightening Sheet](#)

[Contact a Litetronics Representative](#)

### Specifications

Category	Incandescent
Shape	A19
Brand	Rough Service
Part Number	L-128A
Watts	60
Base	MED
Voltage	120
Average Rated Life	20,000
Case Quantity	120
Initial Lumens	560
CRI	100
Finish	Frost
M.O.L.	4.44"
Warranty	2 years

**CUSTOMER REVIEWS:**

There are yet no reviews for this product.

Please log in to write a review.