



Product Number: 12420

Order Abbreviation: 60ARS/2/RP 130V

General Description: Incandescent A19 Bulb Shape Rough Service Inside Frost Finish Medium Aluminum Base 60Watt 130Volt Retail Pack 24Bulbs Per Case 2Bulbs Per Package

Product Information	
Abbrev. With Packaging Info.	60ARS2RP 130V 24/CS 2/SKU
Approx. Lumens	555
Average Rated Life (hr)	1000
Base	Medium
Bulb	A19
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	2.375
Diameter (mm)	60.33
Family Brand Name	ROUGH SERVICE
Filament	C-9
Lamp Finish	Inside Frost
Light Center Length - LCL (in)	2.875
Light Center Length - LCL (mm)	73
Maximum Overall Length - MOL (in)	4.438
Maximum Overall Length - MOL (mm)	112.7125
Nominal Voltage (V)	130.00
Nominal Wattage (W)	60.00



Footnotes

- Incandescent lamps operated at less than rated voltage provide a lower light output, longer life, lower color temperature and are less efficient in terms of lumens per watt.
- @ 120 volts, approximate 53 watts, 420 lumens, 2500 hours