



Part #	RSB75				
Description	A19, 130V, 75W				
Bulb Shape	A-19	Filament	C-9	Base Style	Medium Screw (E26)
Glass Diameter (in)	2.36	MOL[†] (in)	4.25	LCL^{††} (in)	0.00
Glass Diameter (mm)	60	MOL (mm)	108.00	LCL (mm)	0.00
Volts	130	MSCP[‡]	0	Avg Life Hrs	2500
Watts	75	Amps	0.58	RoHS Compliant	
E-Marked	No	Drawing		New Announcement	