

MINIATURE LAMP (TS75) Details



Part #	TS75				
Description	TOUGH SKIN BULB 130V 75W				
Bulb Shape	A19	Filament	C-9	Base Style	MEDIUM SCREW E-26
Glass Diameter (in)	2.36	MOL† (in)	4.25	LCL†† (in)	3.12
Glass Diameter (mm)	60	MOL (mm)	108.00	LCL (mm)	79.20
Volts	130	MSCP ‡	95	Avg Life Hrs	5000
Watts	75	Amps	.577	RoHS Compliant	
E-Marked		Drawing		New Announcement	



&

