



**Product Number:** 13622

**Order Abbreviation:** 25G16.5CM/BL 120V

**General Description:** Incandescent G16.5 Décor Bulb Shape Soft White Finish Candelabra Base 25Watt 120Volt  
24Bulbs Per Case 1Bulb Per Package

Product Information	
Abbrev. With Packaging Info.	25G165CWBL 120V 12/CS 2/SKU
Average Rated Life (hr)	1500
Base	Candelabra
Bulb	G16.5
Class	B (vacuum)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	2.063
Diameter (mm)	52.39
Filament	C-7A
Lamp Finish	Soft White
Maximum Overall Length - MOL (in)	3.000
Maximum Overall Length - MOL (mm)	76.2
Nominal Voltage (V)	120.00
Nominal Wattage (W)	25.00

