



Dependable Power for Any Application

Product Datasheet

460 Δ Primary Volts - 460Y/266 Secondary Volts - 3 \emptyset Drive Isolation Transformer - Three Phase

Catalog #: DTGB07704S



PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R with optional Weather Shield
- Aluminum foil windings
- Aluminum bus bar terminations
- Butt stacked/Step lap core construction
- Covered under Acme's 10 year limited warranty
- Optional Thermal Switch - part # PL79900

BENEFITS

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

UL STANDARD

UL 1561

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	770.00
Primary Voltage:	460Δ
Secondary Voltage:	460Y/266
Frequency:	60 Hz
ANFC Taps:	2
BNFC Taps:	2
Taps % Steps:	2.5%
Max Temperature Rise:	150°C
UL Insulation Class:	220°C

PRODUCT MEASUREMENTS

Height (In./cm):	62.84 (159.6)
Width (In./cm):	54 (137.2)
Depth (In./cm):	41.49 (105.4)

CONFIGURATION

Construction Type:	Ventilated
Mounting Type:	Floor
Weather Shield:	WSA6
Wiring Diagram:	35

PACKAGING

Ship Weight (Lbs/Kg):	4044 (1838.2)
-----------------------	---------------

COMPLIANCES

UL Standard:	UL 1561
UL Listed:	File E12547
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
	www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf