

JC

- Only for Use in Approved Enclosed Halogen Fixtures
- Miniature 2-Pin Base - G4
- Universal Burn Position



Watts	Ushio Ordering Code	Ushio Lamp Description	Dimensions mm			Filament Type	Approx Lumens lm	Color Temp K	Avg Life h	Bulb Finish
			Dia (A)	MOL (B)	LCL (C)					
<b>Miniature 2-Pin Base – G4</b>										
5	1000874	JC6V-5W/G4*	9.0	28.0	19.5	C-6	100	3006	50	Clear
5	1000833	JC12V-5W/G4	9.0	28.0	19.5	C-2R	60	2720	2000	Clear
8	1000878	JC6V-8W/G4*	9.0	28.0	19.5	C-6	163	3168	50	Clear
10	1000856	JC6V-10W/G4	9.0	30.0	19.5	C-6	130	2850	2000	Clear
10	1000857	JC6V-10WH3 (64223)	8.0	31.0	19.5	C-6	150	2900	300	Clear
10	1000531	FHD/ESA, JC6V-10W	9.0	30.0	19.5	C-6	200	3200	100	Clear
10	1003030	JC12V-10W/G4	9.0	30.0	19.5	C-6	120	2800	2000	Clear
10	1000811	JC12V-10W/G4	9.0	28.0	19.5	C-2R	140	2900	2000	Clear
10	1000813	JC12V-10WF/G4	9.0	30.0	19.5	C-6	115	2800	2000	Frosted
10	1000812	JC12V-10W/G4	9.0	28.0	19.5	C-2R	175	2916	300	Clear
15	1000861	JC6V-15W/G4	9.0	28.0	19.5	C-6	300	3138	100	Clear
20	1000532	FHE/ESB, JC6V-20W	9.0	30.0	19.5	C-6	450	3200	100	Clear
20	1000866	JC6V-20W/G4	9.0	30.0	19.5	C-6	280	2850	2000	Clear
20	1000821	JC12V-20W/G4	9.0	30.0	19.5	C-6	350	2850	2000	Clear
20	1000804	JC12V-20W/G4	9.0	30.0	19.5	C-8	350	2850	2000	Clear
20	1000820	JC12V-20WF/G4	9.0	30.0	19.5	C-6	330	2900	2000	Frosted
20	1000844	JC24V-20W/G4	9.0	30.0	19.5	C-6	280	2850	2000	Clear
30	1000867	JC6V-30W/G4	9.0	30.0	19.25	C-6	800	3300	50	Clear
35	1000825	JC12V-35WB/G4	9.0	30.0	19.5	C-6	650	2900	2000	Clear

\* Special Order Item

Originally developed as light sources for optical instruments, JC lamps feature an overall compact design with precise LCL placement. The exceptional brightness of this compact lamp make this series an ideal choice for task light applications.

