

products

- MEDICAL (medical, dental, scientific)
- AVIATION (aircraft, airfield)
- INFRARED (QIR)
- HALOGEN
 - J Type
 - JC Type
 - JD Type
 - JDD & JTT Type
 - JCD Type
 - JDR Type
 - MR Type
 - Elevator
 - Marine
 - Buoy
 - Stage
 - Traffic
- XENON (Festoon, Rigid Loop)
- UV (Germicidal, UVB, Blacklight)
- HID general use (MH, HPS)
- LED (Strip module)
- CUSTOM LAMPS & PARTS

Products » HALOGEN » JD Type » JD-7055

Order Code: JD-7055



JD 130V 50W DC BA15d

Specifications	Images & Figures	Cross References	Additional Information
Lamp Group:			Halogen
Lamp Type:			JD
Voltage (V):			130
Wattage (W):			50
Base:			BA15d
Life Hour:			2000
Color Temp (K):			2750
Lumen (lm):			700
MOL (mm):			48
Diameter (mm):			13
Back to ALL Products			