



24V Halogen solutions Headlamps







Combining vibration resistance with high quality, our **24V Standard** and **Heavy Duty** lighting ranges are robust and dependable for today's trucks and other heavy-duty vehicles. NARVA truck headlamps feature vibration resistance and superior quality. Check out our Standard lamps or our Heavy Duty range when greater strength and durability are required.



Replacement

STANDARD

Value for money

	ECE	Ref. No	V	W	Base	Pieces/PU	Packaging
	H1	487023000	24	70	P14,5s	100	C1
		487024000	24	70	P14,5s	10	B1
	H2	487203000	24	70	X511	100	C1
	H3	487003000	24	70	PK22s	100	C1
	H4	488923000	24	75/70	P43t	100	C1
		488924000	24	75/70	P43t-38	10	B1
	H7	487283000	24	70	PX26d	100	C1
		487284000	24	70	PX26d	10	B1
	R2 Halogen	481323000	24	55/50	P45t-41	100	C1