



Part Number	Size	T Min.	OD	ID Min.	E	B	D Min.	L Min.
A52AE12	½ "	0.109"	0.840"	0.578"	0.852"	0.836"	1.500"	120"
A52AG12	¾ "	0.113"	1.050"	0.780"	1.064"	1.046"	1.750"	120"
A52BA12	1"	0.133"	1.315"	1.004"	1.330"	1.310"	2.000"	120"
A52BC12	1 ¼ "	0.140"	1.660"	1.335"	1.677"	1.655"	2.250"	120"
A52BE12	1 ½ "	0.145"	1.900"	1.564"	1.918"	1.894"	2.500"	120"
A52CA12	2"	0.154"	2.375"	2.021"	2.393"	2.369"	3.000"	120"
A52CE12	2 ½ "	0.203"	2.875"	2.414"	2.890"	2.868"	3.250"	120"
A52DA12	3"	0.216"	3.500"	3.008"	3.515"	3.492"	3.750"	120"
A52DE12	3 ½ "	0.226"	4.000"	3.486"	4.015"	3.992"	4.000"	120"
A52EA12	4"	0.237"	4.500"	3.961"	4.515"	4.491"	4.500"	120"
A52FA12	5"	0.258"	5.563"	4.975"	5.593"	5.553"	5.500"	120"
A52GA12	6"	0.280"	6.625"	5.986"	6.658"	6.614"	6.125"	120"
A52JA12 *	8"	0.322"	8.625"	7.853"	8.670"	8.610"	6.375"	120"

Dimensions are Nominal
 * Not ETL Listed

ETL Listed
 Conforms to UL-651
 NEMA TC2 Compliant
 See NEC Article 352 for use
 Sunlight Resistant
 Max 90° C Wire

Complies with Federal Specification WC-1094



CANTEX
 INC.
 Fort Worth, TEXAS

Schedule 40 Rigid PVC Conduit

Drawn By: D.S. Frank

Date: 7-13-2010