



Carlon®



Plenum-Gard® Flexible Conduit

T&B Catalog Number: CG4X1C-3200
 UPC Number: 79120720033
 Status: Active

Description:

1-1/4" Plenum-Gard® orange corrugated non-metallic flexible conduit with tape, reel length-3200'.



Where To Buy

Enter Zip Code:

Enter Quantity:

Features

- Manufactured from PVDF resin which is extremely durable and resistant to abrasion and mechanical damage before/after cable installation.
- Listed to UL 2024 in accordance with the National Electrical Code for Plenum, Riser, General Purpose and other cabling optical fiber and telecommunication applications as defined in Articles 725, 770, 800 and 820.
- FT-6 Rated

Application

- Plenum, Riser and General Purpose Applications.

General

Material	Non-Metallic
Color	Orange
Reel Type	Wood
Reel Length (feet)	3200
Reel Size (Feet x Width)	66" x 41"
Storage Temperatures	-4° F to 158° F
Handling Temperatures	-4° to 104° F
Pull Tape (lbs)	900

Dimension Information

Size (inches)	1 1/4
Minimum Bend Radius (inches)	3
Minimum O.D. (inches)	1.630
Maximum O. D. (inches)	1.650

Packaging

Order Multiple	3200
Outer Package	3200
T&B Sold in UOM	Feet
T&B Weight Per UOM	0.22 lbs. Each

Notes

- *Note No UV protection, not suitable for outdoor use.
- **Note Do NOT store outside.
- ***Note Installed cables must be plenum rated and the UL Listing must be printed on the product. Abandoned cables MUST be removed (Reference NEC).

Certifications

RoHS Compliance [Yes](#) [Generate Compliance Certificate](#)

Certifications



File Nbr:
E 13938

HOME

[Global Site](#)

[Report Issue](#)

LOGIN

[T&B Access \(Dist only\)](#)

[Suppliers](#)

[MyTNB](#)

RESOURCES

[Catalog PDFs](#)

[End User Toolkit](#)

[Solution Set Brochures](#)

[Vertical Market Brochures](#)

[Where To Buy](#)

SUPPORT

[Contact Us](#)

[Global Locations](#)

[Product Support](#)

[Tool Services](#)

[Terms](#)

COMPANY

[About Us](#)

[Careers](#)

[Employees](#)

[News](#)

Thomas & Betts

© 2012 Thomas & Betts Corporation
No material from this site may be copied, distributed or in any way used without the expressed prior permission of Thomas & Betts.

