



# Carlon®



## Riser-Gard® Flexible Raceway

T&B Catalog Number: DJ4X1C-2800  
 UPC Number: 79120735013  
 Status: Active

### Description:

2" Riser-Gard® orange corrugated non-metallic flexible raceway with tape, reel length-2800'.



**Where To Buy**

Enter Zip Code:

Enter Quantity:

### Features

- UL Listed and is available with tape pre-installed.
- Listed to UL 2024 in accordance with the National Electrical Code per Articles 725, 770, 800 and 820 for Riser, General Purpose and other cabling optical fiber/telecommunication applications.
- FT-4 Rated

### Application

- Riser-Gard is suitable for use in vertical runs in a shaft or between floors, as well as areas other than the plenum.
- Riser and General Purpose

### General

Material	Non-Metallic
Color	Orange
Reel Type	Steel
Reel Length (feet)	2800
Reel Size (Feet x Width)	84" x 45"
Storage Temperatures	-4° F to 158° F
Handling Temperatures	-4° to 104° F
Pull Tape (lbs)	900

### Dimension Information

Size (inches)	2
Minimum Bend Radius (inches)	12
Minimum O.D. (inches)	2.350
Maximum O. D. (inches)	2.400

### Packaging

Order Multiple	2800
Outer Package	2800
T&B Sold in UOM	Feet
T&B Weight Per UOM	0.34 lbs. Each

### Application Support

T&B Sales Drawings	<a href="#">wsd-ac04182</a>
--------------------	-----------------------------

### Notes

- \*Note No UV protection, not suitable for outdoor use.
- \*\*Note Do NOT store outside.
- \*\*\*Note Installed cables must be of suitable rating for the application.

### Certifications

RoHS Compliance [Yes](#) [Generate Compliance Certificate](#)

### Certifications



File Nbr:  
E 13938

HOME

[Global Site](#)

[Report Issue](#)

LOGIN

[T&B Access \(Dist only\)](#)

[Suppliers](#)

[MyTNB](#)

RESOURCES

[Catalog PDFs](#)

[End User Toolkit](#)

[Solution Set Brochures](#)

[Vertical Market Brochures](#)

[Where To Buy](#)

SUPPORT

[Contact Us](#)

[Global Locations](#)

[Product Support](#)

[Tool Services](#)

[Terms](#)

COMPANY

[About Us](#)

[Careers](#)

[Employees](#)

[News](#)

**Thomas & Betts**

© 2012 Thomas & Betts Corporation  
No material from this site may be copied, distributed or in any way used without the expressed prior permission of Thomas & Betts.

