

CleanVia®

Sustainable in Nature . Proven in Industry

DEGREASER AND ALL PURPOSE CLEANER

Construction
Facility Maintenance
Institutional & Office

HIGH EFFICACY DEGREASER

100.38% efficiency @ 25% in solution
Test Method ASTM D4488-A5
Eco-Logo certified for performance
Formula proven in Industry for over ten years

NO VOC's

Test Method USEPA 8240 / 8260
Tested @ .0003% Volatile Organic Compounds

TOOL SAFE

Non-detergent, non-oxidizing formula
Easily wipe clean tools and equipment
Safely clean parts including plastics

USER FRIENDLY

Safe for use as a hand and body wash
Remove stains from fabric and clothing

100% PLANT DERIVED

Exclusive Safflower and Oat oil formula
Contains no petroleum or butyls
Readily Biodegradable protocol EPS 1/RM/25

REDUCE ENERGY

Formula does not form an emulsion
Less water is required to rinse
Available as a true concentrate

Super Concentrate 100% in solution
Cleaner Degreaser 25% in solution
All Purpose Cleaner 6.25% in solution



CONTACT CleanVia, Inc. www.cleanvia.com 503-288-0000 info@cleanvia.com

P.O. Box 69344 Portland, OR 97239