

Disaster Recovery & Restoration Cords

Made to meet
OSHA
Specifications

For use in disaster recovery, restoration, renovation or maintenance projects requiring temporary, portable power.



CAT NO	LENGTH	DESCRIPTION	STD PACK	WT	MALE END	FEMALE END	POWER FROM
01854~	10 ft.	10/4 SE00W 14-30P L1430R UL/CSA	4	3.99	14-30P	L14-30R	Dryer Outlet
01824~	10 ft.	10/4 SE00W 14-30P CA50A UL/CSA	4	4.28	14-30P	CA 50A Twist	
01864~	10 ft.	10/4 SE00W 14-50P L14-30R UL/CSA	4	3.99	14-50P	L14-30R	Range Outlet 50A generator w/straight blade output
01834~	10 ft.	6/3 & 8/1 SEOW 14-50P CA50A	4	6.38	14-50P	CA 50A Twist	
1493*	25 ft.	10/4 STW Yellow Jacket L14-30P L14-30R	2	8.24	L14-30P	L14-30R	30A Generator
01844~	10 ft.	10/4 SE00W L14-30P CA50A UL/CSA	4	4.11	L14-30P	CA 50A Twist	

* Part number 1493 is UL / cUL

~Assembled in the U.S.A.

Generator Power Cords

Made to meet
OSHA
Specifications



01910

CAT NO	WIRE GA/COND	WIRE TYPE	COLOR	LENGTH IN FT	PACKAGE TYPE	125V RATING	MASTER PACK	MASTER WT	MASTER PACK CUBE
<i>Temporary power cord with three 15 amp receptacles and one male 5-15P plug engineered to work exclusively with generators or other equipment rated to or less than 15 amps.</i>									
01910*	12/3	SJTW	Yellow	25	Card	15A	12	44.5	2.20
<i>Temporary power cord with three 15 amp receptacles and one male 5-20P plug engineered to work exclusively with generators or other equipment rated to or less than 15 amps.</i>									
01911	10/3	SJTW	Yellow	25	Card	15A	6	36.5	1.41
<i>Temporary power cord with three 15 amp receptacles and one male L5-30P plug engineered to work exclusively with generators or other equipment rated to or less than 15 amps.</i>									
01912	10/3	SJTW	Yellow	25	Card	15A	6	35.6	1.41

* UL Listed

Twist-To-Lock Extension Cords

Made to meet
OSHA
Specifications



09058/09059



NEMA L5-20R
20A 125V

CAT NO	WIRE GA/COND	WIRE TYPE	COLOR	LENGTH IN FT	PACKAGE TYPE	125V RATING	MASTER PACK	MASTER WT	MASTER PACK CUBE
SJTW Extension Cords (NEMA L5-20P to NEMA L5-20R)									
09208	12/3	SJTW	Yellow	50	Box	20A	6	41	1.94
09209	12/3	SJTW	Yellow	100	Box	15A	4	52	1.77
09058	10/3	SJTOW	Yellow	50	Disc	20A	2	22	1.66
09059	10/3	SJTOW	Yellow	100	Disc	20A	2	45	2.33
STW Extension Cords, (NEMA L5-20P to NEMA L5-20R) - 600 Volt Rated									
09028	12/3	STW	Yellow	50	Box	20A	4	40	1.93
09029	12/3	STW	Yellow	100	Box	15A	3	60	2.6

Vinyl "Y" and "W" Adapters

Made to meet
OSHA
Specifications



09019

09018

CAT NO	WIRE GA/COND	WIRE TYPE	COLOR	LENGTH IN FT	PACKAGE TYPE	125V RATING	MASTER PACK	MASTER WT	MASTER PACK CUBE
15A "Y" Adapter									
09018	12/3	STW	Yellow	2	Sleeve	15A	12	20	1.96
15A "W" Adapter									
09019	12/3	STW	Yellow	2	Sleeve	15A	12	25	1.09



1530 Shields Drive • Waukegan, IL 60085 • 800-323-9355 • www.colemancable.com