



PRODUCT SPECIFICATION

COLEMAN PART NUMBER: See table below
DESCRIPTION: 16/2 w/gnd SPT-3 replacement power supply cord
APPROVALS: UL Listed (UL 817)

CONSTRUCTION PARAMETERS:

Conductor: 16 AWG, 26/30 bunched bare copper
 Conductor O.D. (nom): 0.063"
 Insulated ground conductor O.D. (nom): 0.091"
 Insulation material: PVC, gray
 Overall cable dimensions (nom): 0.181 x 0.413"

Cord length: See table below
 Attachment plug configuration: NEMA 5-15P, see chart below
 Plug material: PVC, gray
 Open end configuration: 1.5" separation, 0.38" strip

ELECTRICAL PROPERTIES:

Temperature rating: -20 to +60 °C
 Nominal operating voltage: 125 VAC
 Maximum operating current: 13 A
 Maximum operating wattage: 1625 W

CATALOG NUMBERS

Catalog number	Cord length	Plug configuration
09723	3 ft	Right angle
09724	4 ft	
09726	6 ft	
09733	3 ft	Straight
09734	4 ft	
09736	6 ft	

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Inc. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Inc.

CUSTOMER APPROVAL: Approved by: _____ Date: _____
 Title: _____