

The Seoprene® Portable Cord Series

Coleman Cable's Seoprene® Thermoplastic Elastomer cord products are technologically advanced to meet the requirements of today's demanding commercial and industrial applications. They provide the chemical resistance characteristics of PVC with highly flexible properties.

FEATURES:

- **Easy to Strip**
- **Lighter in Weight**
- **Outstanding flexibility**
- **Non-wicking polypropylene fillers**
- **All-weather protection from -50°C to 105°C**



PROPERTIES	SJEOW	SEOOW
Flexibility	Superior	Superior
Oil Resistance Insulation	Superior	Superior
Oil Resistance Jacket	Superior	Superior
Abrasion Resistance	Superior	Superior
Tear Resistance	Superior	Superior
Ozone Resistance	Superior	Superior
Low-Temperature Flexibility	Very Good	Very Good

Seoprene® 105 Black

It is perfect for general indoor and outdoor temporary power applications such as industrial controls, motor controls, compressors, robotic systems and portable tools.



PART NUMBER	DESCRIPTION	STRANDING	NOMINAL INSULATION THICKNESS	NOMINAL JACKET THICKNESS	NOMINAL OD	AMPACITY	WT/M'
23325	18/3 SJEOOW	16/30	.031	.032	.310	10	55
23425	18/4 SJEOOW	16/30	.031	.032	.335	7	66
23326	16/3 SJEOOW	26/30	.031	.032	.335	13	67
23426	16/4 SJEOOW	26/30	.031	.032	.360	10	78
23327	14/3 SJEOOW	41/30	.031	.032	.370	18	84
23427	14/4 SJEOOW	41/30	.031	.032	.400	15	104
23328	12/3 SJEOOW	65/30	.031	.047	.435	25	123
23428	12/4 SJEOOW	65/30	.031	.047	.475	20	157
23329	10/3 SJEOOW	104/30	.046	.062	.580	30	216
23429	10/4 SJEOOW	104/30	.046	.062	.640	25	276
22325	18/3 SEOOW	16/30	.031	.062	.365	10	69
22425	18/4 SEOOW	16/30	.031	.062	.395	7	81
22326	16/3 SEOOW	26/30	.031	.062	.390	13	81
22426	16/4 SEOOW	26/30	.031	.062	.420	10	99
30506	16/5 SEOOW	26/30	.031	.085	.495	8	135
22327	14/3 SEOOW	41/30	.046	.082	.525	18	149
22427	14/4 SEOOW	41/30	.046	.082	.575	15	183
22328	12/3 SEOOW	65/30	.046	.097	.595	25	199
22428	12/4 SEOOW	65/30	.046	.097	.645	20	242
22329	10/3 SEOOW	104/30	.046	.095	.655	30	259
22429	10/4 SEOOW	104/30	.046	.095	.705	30	316

Applications: Heavy machine tools; compressors; portable tools; robotics; motor controls.
Suitable for use in wet locations including submersion in water.



Seoprene®

Packaging Options

Coleman Cable offers four types of packaging options.

- Signa-Coil
- Reel-in-box
- Pull-out box (Rabbit pull)
- Reels

All provide fast and easy cable access. Kinks and twists are eliminated. You get tangle-free cable delivery each and every time. These durable, compact designs save on installation time while reducing waste and material costs. They can be easily stacked to save room.

* Not all options are available for each product



Coleman Cable Part Legend

XXXXXX-XX-XX



Put-ups

Put-ups	Code
Reel, 250 ft	04
Reel, 500 ft	05
Reel, 1,000 ft	06
Reel-in-box, 1,000 ft	16
RabbitPull™ Pull-Box, 500 ft	45
RabbitPull™ Pull-Box, 1,000 ft	46
SignaCoil™ 500 ft	55
SignaCoil™ 1,000 ft	56

Colors

Colors	Code	Colors	Code
White	01	Pink	11
Yellow	02	Purple	13
Orange	03	Clear	18
Red	04	Fluorescent	21
Green	05	Pink	21
Blue	06	Ivory	22
Brown	07	Natural	23
Black	08	Beige	33
Gray	09	Red Striped	44
		CorraClad™	44

