

Seoprene® 105 Control Cable



Cable ranges from 18-10 AWG with 5 or more conductors. Provides lightweight flexibility and mechanical toughness in a multi-conductor construction that is easy to strip. Rated 600V with temperature ratings from -50C to 105C. Applications include power in processing facilities, push-button line controls, 600V control and instrumentation, temperature, motor and robotic control systems. UL Listed, CSA Certified, MSHA approved for flame resistant mining applications.



CAT NO	SIZE	TYPE	JACKET COLOR	WT/ 1000'
30505-xx-08	18/5	SE00W	Black	113
30605-xx-08	18/6	SE00W	Black	119
30805-xx-08	18/8	SE00W	Black	151
31005-xx-08	18/10	SE00W	Black	168
31205-xx-08	18/12	SE00W	Black	212
31405-xx-08	18/14	SE00W	Black	235
31605-xx-08	18/16	SE00W	Black	277
30506-xx-08	16/5	SE00W	Black	140
30606-xx-08	16/6	SE00W	Black	158
30706-xx-08	16/7	SE00W	Black	165
30806-xx-08	16/8	SE00W	Black	190
31006-xx-08	16/10	SE00W	Black	242
31206-xx-08	16/12	SE00W	Black	288
31406-xx-08	16/14	SE00W	Black	311
31606-xx-08	16/16	SE00W	Black	355
30507-xx-08	14/5	SE00W	Black	232
30607-xx-08	14/6	SE00W	Black	269
30707-xx-08	14/7	SE00W	Black	280
31007-xx-08	14/10	SE00W	Black	423
31207-xx-08	14/12	SE00W	Black	465
30508-xx-08	12/5	SE00W	Black	302
30608-xx-08	12/6	SE00W	Black	343
30808-xx-08	12/8	SE00W	Black	416
30509-xx-08	10/5	SE00W	Black	387

Put-up: xx= 250' (04); 500' (05); 1000' (06)

Lamp Cord



For use with lamps and other small appliances.



60000

CAT NO	WIRE GAUGE	DESCRIPTION	JACKET COLOR	STRANDING	NOMINAL WALL	NOMINAL O.D.	LENGTH IN FT	MASTER WT
60000-66-01	18/2	SPT-1	White	41/34	.033	.115 x .250	250	7
60000-66-07	18/2	SPT-1	Brown	41/34	.033	.115 x .250	250	7
60000-66-08	18/2	SPT-1	Black	41/34	.033	.115 x .250	250	7
60000-66-18*	18/2	SPT-1	Clear	41/34	.033	.115 x .250	250	7
60000-66-19*	18/2	SPT-1	Gold	41/34	.033	.115 x .250	250	7
60000-66-21*	18/2	SPT-1	Silver	41/34	.033	.115 x .250	250	7
60126-66-01	16/2	SPT-2	White	26/30	.048	.156 x .307	250	10
60126-66-07	16/2	SPT-2	Brown	26/30	.048	.156 x .307	250	10
60126-66-08	16/2	SPT-2	Black	26/30	.048	.156 x .307	250	10

* Not CSA Listed

